


MENTOR® BECKER™ Expander/ Breast Implants

SILTEX™ CONTOUR PROFILE™ BECKER™ 35 Expander/Implants, Cohesive II™

(35% Silicone Gel, Cohesive II™, in outer lumen,
65% Saline in inner lumen)



Volume cc	Gel Volume cc	TEMPORARY OVEREXPANSION VOLUMES		Total Saline cc	Total Gel- Saline cc	Width cm	Height cm	Proj. cm	Cat.#
		Max Saline cc	Total Gel- Saline cc						
290	100	235	335	170-190	270-290	12,0	10,5	5,3	324-1205
325	110	270	380	190-215	300-325	12,5	10,9	5,5	324-1255
365	125	300	425	215-240	340-365	13,0	11,3	5,7	324-1305
400	130	335	465	240-270	370-400	13,5	11,8	5,9	324-1355
460	160	375	535	270-300	430-460	14,0	12,2	6,2	324-1405
565	195	460	655	330-370	525-565	15,0	13,1	6,6	324-1505

Note: Individual implant dimensions may vary slightly in products of this type.
Not all units will conform exactly to the dimensions noted above